



Technical data sheet – *PE-brine distributor*



Standard equipment

Outward: ball valves PVC to lock-up one single circuit
Return Flow: ball valves or flowmeter (brass or plastic)

Backfilling and deaeration (constructed as a ball valve PVC 1" male)

Connection probes: O.D. 32mm or O.D. 40mm, designed as a open tube end

PE-brine distributor	Manifold - Ø	Connection heat pump
2-8	O.D. 63mm	O.D. 63mm
9-16	O.D. 90mm	O.D. 90mm
17-25	O.D. 125mm	O.D. 125mm

PE-brine distributor > 26- ports and one-off production on request

Against extra charge: Shut-off valve, fixation set

MANIFOLDS ARE PRESSURE-TESTED

**WARNING ! THE DISTRIBUTOR CONNECTIONS HAVE TO BE INSTALLED ZERO-POTENTIAL.
READ, KEEP, HEED, AND FOLLOW ALL INSTRUCTIONS OBTAINED IN THE MANUAL/USERS GUIDE.**