



## Technical data sheet – *PE-chamber BASIC*



Circles	2	3	4
Design	accessible until 200kg		
Material	PE		
Chamber Height	520mm	620mm	720mm
Chamber foot point	400x400mm		
Connection Probes	from Ø 25mm		
Connection heat pump	Ø 63mm		
Spout- distance	100mm [Spout welded with a chamber wall]		
Delivery	Delivery on throw-away palett		

### Standard equipment

Outward: ball valves PVC to lock-up one single circuit  
Return flow: ball valves or flowmeter (brass or plastic)

Backfilling and deaeration (constructed as a ball valve PVC 1" male)

Connection probes: O.D. 32mm or O.D. 40mm  
Connection heat pump / Manifold: Ø 63mm

**MANIFOLDS ARE PRESSURE-TESTED**

**WARNING ! THE DISTRIBUTOR CONNECTIONS HAVE TO BE INSTALLED ZERO-POTENTIAL.  
READ, KEEP, HEED, AND FOLLOW ALL INSTRUCTIONS OBTAINED IN THE MANUAL/USERS GUIDE.**